

nVent ERIFLEX Flexibar End Cover



FEATURES

End cover for nVent ERIFLEX Flexibar and Insulated Power Braid

Allows for visual inspection of connection

Easy fitting after fixing

Halogen free

RoHS compliant

Material: Polycarbonate
Flammability Rating: UL® 94V-0



SPECIFICATIONS

Catalog Number	Article Number	Conductor Width	Unit Weight
ENDCOV20	541774	20 mm	0.19 kg
ENDCOV24	541775	24 mm	0.22 kg
ENDCOV32	541776	32 mm	0.26 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE