


# Assembly Parts for Rugged Components



Assembly parts with thread-locking compound for rugged Side Panel, horizontal rail, cover plates, rear angle.

## FEATURES

Screws for the following fixings: Rugged side panel - horizontal rail, Rugged side panel - cover plate, Rugged side panel - rear angle

**Product Type:** Assembly Kit  
**Product Family:** EuropacPRO



## SPECIFICATIONS

| Catalog Number | Type              | Length | Package Quantity | Thread Size | Finish      | Material        | Works With |
|----------------|-------------------|--------|------------------|-------------|-------------|-----------------|------------|
| 24566-105      | Countersunk Screw | 7mm    | 100              | M4          |             | Stainless Steel | Sub racks  |
| 24566-104      | Panhead Screw     | 8mm    | 100              | M4          |             | Stainless Steel | Sub racks  |
| 24566-106      | Countersunk Screw | 10mm   | 100              | M4          |             | Stainless Steel | Sub racks  |
| 24566-103      | Panhead Screw     | 10mm   | 100              | M4          |             | Stainless Steel | Sub racks  |
| 24566-101      | Countersunk Screw | 14mm   | 100              | M4          |             | Stainless Steel | Sub racks  |
| 24566-102      | Panhead Screw     | 14mm   | 100              | M4          |             | Stainless Steel | Sub racks  |
| 24566-100      | Countersunk Screw | 18mm   | 100              | M4          |             | Stainless Steel | Sub racks  |
| 24560-140      | Square Nut        |        | 100              |             | Zinc Plated | Steel           | Sub racks  |

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**