

nVent CADDY EZ Riser



The nVent CADDY EZ Riser is a multi-purpose clamp designed to secure and support vertical pipe runs. This unified solution can be installed in several approved orientations and serves as a standard, standoff, or close-quarters riser—effectively functioning as three clamps in one. Ready-to-use out of the box, the nVent CADDY EZ Riser features pre-drilled threaded rod holes for standoff installations and score marks for simple ear removal in spaces where full-sized riser clamps do not fit.

Contractors can enjoy simplified material handling with a multi-functional clamp that allows for various orientations and retains listing even when ears are removed.

VLASTNOSTI

Only one tool needed to tighten due to serrated wash-heads

Installs up to 60% faster than standard riser clamps

Integrated second set of bolt holes allow the assembly to adapt from a riser clamp into a stand-off support easily

No need to stock and use separate part families for standard and close-quarter clamps to offer a full range of listed parts

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

Povrchová úprava: Electrogalvanized
Materiál: Ocel



SPECIFIKACE

Katalogové číslo	Article Number	Outer Diameter (OD)	Hole Size (HS)	A	B	C	Static Load
EZR0250	179231	73 mm	9.9 mm	279.4 mm	190.5 mm	25.4 mm	1735N
EZR0300	179232	88.9 mm	9.9 mm	298.5 mm	206.4 mm	25.4 mm	2400N
EZR0200	179230	60.3 mm	9.9 mm	260.4 mm	177.8 mm	25.4 mm	1100N
EZR0050	179225	21.3 mm	9.9 mm	215.9 mm	130.2 mm	22.2 mm	1100N
EZR0150	179229	48.3 mm	9.9 mm	250.8 mm	158.8 mm	22.2 mm	1100N
EZR0125	179228	42.2 mm	9.9 mm	241.3 mm	152.4 mm	22.2 mm	1100N



Katalogové číslo	Article Number	Outer Diameter (OD)	Hole Size (HS)	A	B	C	Static Load
EZR0100	179227	33.4 mm	9.9 mm	228.6 mm	142.9 mm	22.2 mm	1100N
EZR0075	179226	26.7 mm	9.9 mm	228.6 mm	136.5 mm	22.2 mm	1100N
EZR0500	179235	141.3 mm	13.2 mm	368.3 mm	298.5 mm	38.1 mm	5200N
EZR0600	179236	168.3 mm	13.2 mm	406.4 mm	323.9 mm	38.1 mm	6900N
EZR0400	179234	114.3 mm	13.2 mm	330.2 mm	254 mm	31.8 mm	3600N

DALŠÍ PODROBNOSTI O PRODUKTU

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Use of a socket or driver is recommended for installation.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

