


Speedway Cable Ladder Equal Cross



VLASTNOSTI

Creates a four way intersection for cable tray

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant


Responsive design and layout services, including seismic

Povrchová úprava: Hot-Dip Galvanized
Materiál: Ocel



SPECIFIKACE

Katalogové číslo	Article Number	Width (W)	A	B	C	D	E
CL110X600ECHD	840830	600 mm	1350 mm	530 mm	1407 mm	80 mm	110 mm
CL110X450ECHD	840820	450 mm	1200 mm	530 mm	1195 mm	80 mm	110 mm
CL110X150ECHD	840800	150 mm	900 mm	530 mm	771 mm	80 mm	110 mm
CL110X750ECHD	840840	750 mm	1500 mm	530 mm	1619 mm	80 mm	110 mm
CL110X900ECHD	840850	900 mm	1650 mm	530 mm	1831 mm	80 mm	110 mm
CL110X300ECHD	840810	300 mm	1050 mm	530 mm	983 mm	80 mm	110 mm



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

