

Portable Rail Grinder, Two-Cycle Gas-Powered



VLASTNOSTI

Strong 39cc two-cycle engine

Power head handle incorporates base plate to protect engine from damage

Lightweight design

Anti-vibration handle reduces operator fatigue and helps provide proper balance while operating the grinder

Stronger shaft increases durability of operation

Increased grinding wheel stability reduces vibration and wear during operation

One piece of equipment to grind head and web

Maximum wheel speed is 6,000 rpm

Adjustable grinding wheel guard rotates 360° and allows operation in tight areas

SPECIFIKACE

Katalogové číslo	Article Number	Typ	Unit Weight
SBG150WC	715409	Grinder with Storage Case	14.6 kg

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500