

# 19" Assembly Kit M6



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

## VLASTNOSTI

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

**Product Type:** Assembly Kit  
**Povrchová úprava:** Pozinkovaná Ocel



## SPECIFIKACE

Table 1/2

| Katalogové číslo | Length | Množství v balení | Thread Size | Materiál  | Produktová řada                                                                                                           | Typ                     |
|------------------|--------|-------------------|-------------|-----------|---------------------------------------------------------------------------------------------------------------------------|-------------------------|
| 21120-196        | 16mm   | 4                 | M6          | Ocel      |                                                                                                                           | Mounting Kit, Grounding |
| 21190-095        |        | 4                 | M6          | Ocel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor           | Mounting Kit            |
| 21120-213        |        | 4                 | M6          | Ocel      |                                                                                                                           | Mounting Kit            |
| 21100-435        |        | 8                 | M6          | Ocel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor | Mounting Kit            |
| 21120-199        | 13mm   | 100               | M6          | Ocel      |                                                                                                                           | Mounting Kit, Grounding |

| Katalogové číslo | Length | Množství v balení | Thread Size | Materiál  | Produktová řada                                                                                                           | Typ                     |
|------------------|--------|-------------------|-------------|-----------|---------------------------------------------------------------------------------------------------------------------------|-------------------------|
| 21120-197        | 16mm   | 32                | M6          | Ocel      |                                                                                                                           | Mounting Kit, Grounding |
| 21120-198        | 16mm   | 50                | M6          | Ocel      |                                                                                                                           | Mounting Kit, Grounding |
| 21190-435        |        | 32                | M6          | Ocel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor           | Mounting Kit            |
| 21101-810        |        | 100               | M6          | Ocel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor | Mounting Kit            |
| 21101-809        |        | 50                | M6          | Ocel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor | Mounting Kit            |
| 21120-215        |        | 32                | M6          | Ocel      |                                                                                                                           | Mounting Kit            |
| 21120-214        |        | 50                | M6          | Ocel      |                                                                                                                           | Mounting Kit            |
| 21120-216        |        | 100               | M6          | Ocel      |                                                                                                                           | Mounting Kit            |

Table 2/2

| Katalogové číslo | Works With                                                          | Certifications |
|------------------|---------------------------------------------------------------------|----------------|
| 21120-196        | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21190-095        | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS           |
| 21120-213        | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21100-435        | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS           |
| 21120-199        | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21120-197        | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21120-198        | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21190-435        | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS           |
| 21101-810        | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS           |
| 21101-809        | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS           |
| 21120-215        | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21120-214        | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21120-216        | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**