

Collar Screw, Knurled Head Short Version



Integrated load spreading, replaces separate washer.
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

VLASTNOSTI

For assembly of partial width front panels

For EuropacPRO and RatiopacPRO

Knurled head for manual screwing / unscrewing

Works With: Front Panels
Typ: Screw
Product Type: Screw



SPECIFIKACE

Table 1/2

Katalogové číslo	Length	Materiál	Povrchová úprava	Množství v balení	Thread Size	Hloubka
21101-749	12.3mm	Brass, Lead Free	Nickel Plated	100	M2.5	18.3mm
21101-106	11mm	Ocel			M2.5	
21100-268	11mm	Brass	Nickel Plated	100	M2.5	

Table 2/2

Katalogové číslo	Výška	Šířka	Torque	Certifications
21101-749	8mm	8mm	0.3N·m	RoHS
21101-106				
21100-268				

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná

instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE