

DC Fan

Axial fan, 119 mm, with DC input. Replacement part for 1 U fan trays.

VLASTNOSTI

Axial 119 mm DC fan, with plug for connection cable



SPECIFIKACE

Table 1/2

Katalogové číslo	Works With	Šířka	Length	Výška	Napětí stejnosměrné	Průtok vzduchu
60713-600	19" Fan Trays	119mm	119mm	32mm	12V	140m³/h
20713-242	19" Fan Trays	119mm	119mm	38mm	48V	184m³/h
20713-241	19" Fan Trays	119mm	119mm	38mm	12V	184m³/h
20713-240	19" Fan Trays	119mm	119mm	38mm	24V	184m³/h
20713-172	19" Fan Trays	119mm	119mm	25.5mm	24V	171m³/h

Table 2/2

Katalogové číslo	Noise Level	Power	Max Static Pressure	Okolní teplota	Množství v balení
60713-600	39dB(A)	8W	46Pa	70°C	1
20713-242	42dB(A)	8W	68Pa	70°C	1
20713-241	42dB(A)	8W	68Pa	70°C	1
20713-240	42dB(A)	8W	68Pa	70°C	1
20713-172	50.5dB(A)	7W	50.5Pa	70°C	1

DALŠÍ PODROBNOSTI O PRODUKTU

Please order connection cable and protective grille separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE