

Varistar CP MIL 901E Cabinet, Military Certified for Shock, Vibration, EMC, and Corrosion



KATALOGOVÉ ČÍSLO

10630-049

Cabinet with military certification for battle readiness and surviving harsh environments. The enclosures are for frigate, airforce and military applications.

Globally military organizations maintains a comprehensive list of standards for equipment deployed in military applications. By selecting equipment qualified to these standards, design engineers can ensure COTS solutions already meet the minimum requirements to protect mission critical systems.

VLASTNOSTI

NTS tested to MIL-DTL-901E for DSSM drop table test with weight loading of 460 KGs

NTS tested to Test Procedure TP-PR168728-00 for EMI Shielding - Complies with MIL-STD-461G

NTS tested to Mil-STD-810H for Corrosion Resistance

NTS tested to Mil-STD- 167-1A for vibration

Doubly protected against corrosion, zinc-plated and powder-coated

4 shock absorbers at bottom and 2 shock absorbers at top

Rear panel horizontally partitioned in 3 parts - Top cover plate covering the shock absorber fixing area, Bottom cover plate for cable ducting, Middle rear panel closing the gap between the cover plates

EMC Bottom plate adapted with through holes to connect the shock absorbers directly to the frame

VLASTNOSTI PRODUKTU

Product Type: Cabinet

Produktová řada: Varistar CP

Frame Material: Ocel

Frame Color: Black Grey

Frame Color Code: RAL 7021

Cladding Material: Ocel

Cladding Color: Black Grey

Cladding Color Code: RAL 7021

Rack Height: 42U

Výška: 2000mm

Šířka: 600mm

Hloubka: 800mm

Static Load: 1600kg

Dynamic Load: 460kgf

Stupeň krytí: IP55

Complies With: IEC 60529; MIL-S-901E; MIL-STD-461G; MIL-STD-810E; MIL-STD-167

Povrchová úprava: Strukturovaný Práškový

Materiál: Ocel; Stainless Ocel

Net Weight: 173.955kg

Množství v balení: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE