

# 19" Fan Unit, 1 U, Remote Control and Monitoring, 6 Fans, 100-240 VAC

## KATALOGOVÉ ČÍSLO

**10713-554**

Fan Unit with ModBus interface for installation into a 1 U space within the Cabinet

## VLASTNOSTI

Fan speed temperature controlled

ModBus Interface for Remote Monitoring and Control

Temperature threshold for the fan control adjustable on the front panel

Signaling of fan failure and over temperature by 2 LEDs and potential-free relay outputs

Integrated power supply with wide range input (100 V – 240 V)

Less than 1 U (42 mm) to enable mounting on sliding guide rails or drawer

2 NTC temperature sensors with Cables included



## VLASTNOSTI PRODUKTU

Product Type: Fan Unit

Vstupní napětí AC: 100 – 240V

Průtok vzduchu: 1089m³/h

Noise Level: 59.5dB(A)

Power: 97W

Max Static Pressure: 78Pa

Okolní teplota: -10 to 70°C

Lifespan, L10 @ 40 C: 99558h

Množství v balení: 1

Povrchová úprava: Aluminum-Zinc Plated; Anodized

Gross Weight: 5.2kg

Materiál: Ocel; Hliník

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**