


**Front Panel, Shielded, Side Hinged, 6 U, 84 HP,
2.5 mm, Al, Front Anodized, Rear Conductive**



KATALOGOVÉ ČÍSLO

20848-617

Front panel with textile EMC gasket, side hinged assembly.

VLASTNOSTI

Front panel with textile EMC gasket

Enables mounting onto the horizontal rails

Suitable for subracks and cases

Hinges can be fitted on left or right



VLASTNOSTI PRODUKTU

Rack Height: 6U

Množství v balení: 1

Accessory Type: Front panel

Mounting: Hinged, Side

Gasket Type: Textile EMC

Front Finish: Anodized

Rear Finish: Conductive

Treated Edges: No

Hloubka (D): 2.5mm

EMC Shielding: No (Retrofittable)

Povrchová úprava: Anodized; Passivated

Výška (H): 261.8mm



Materiál: Hliník

Product Type: Front Panel

Typ: Front Panel without Handle

Net Weight: 0.99kg

DIAGRAMS



Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE