

# Rack Safety Plus, 3 U, 230 V AC, C20, C13/C19

## KATALOGOVÉ ČÍSLO

**21270-003**

The nVent SCHROFF Rack Safety Plus unit is a 19" power distribution unit used to supply AC mains power to electrical or electronic devices as a central power switch. In addition it is equipped with an emergency stop function.

## VLASTNOSTI

19", 3 U Power Distribution Unit with Emergency Stop function

Supplies AC mains power to electrical or electronic devices as a central power switch

400 V 3-phase or 230 V 1-phase mains input with mains fuses

AC outputs with different connector types, switched by ON/OFF switch

Permanent AC Outputs (Service)

All outputs are protected by circuit breakers

The emergency stop function meets the requirements of EN 60947-5-1 and EN 60204-1 and is vandalism-proof

An additional external emergency stop push button can be connected to the system



## VLASTNOSTI PRODUKTU

Product Type: Power Distributor

Works With: Varistar CP; Novastar

Function: Emergency Stop

Vstupní napětí AC: 230V

Počet fází: 1

EMC Filter: No

Surge Arrester: No

Inrush Current Limiter: No

Residual Current Device: Yes

Circuit Breaker Cover: No

Rack Height: 3U

Typ zásuvky: IEC C13

Accessory Type: Power distribution accessories

Net Weight: 12kg

Množství v balení: 1

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

## DALŠÍ PODROBNOSTI O PRODUKTU

For exact configuration of optional features and example configuration please refer to the item(s) delivered table.

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE