

EuropacPRO 19" Subrack Kit for Backplane, Retrofit Shielding

Non-shielded subrack for backplane mounting.



VLASTNOSTI

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Rear horizontal rail for backplane mounting with insulation strip

Aluminum construction

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Povrchová úprava:	Anodized; Passivated
EMC Shielding:	No
Product Type:	Subrack/Chassis



SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Hloubka	Množství v balení	For Mounting	Board Depth	Gasket Type
24563-132	3U	235mm	1	Backplane	160mm, 220mm	Stainless Steel EMC (retrofittable)
24563-133	3U	295mm	1	Backplane	160mm, 220mm, 280mm	Stainless Steel EMC (retrofittable)
24563-134	3U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC (retrofittable)
24563-135	3U	415mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC (retrofittable)
24563-136	3U	475mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC (retrofittable)
24563-431	6U	175mm	1	Backplane	160mm	Stainless Steel EMC (retrofittable)
24563-432	6U	235mm	1	Backplane	160mm, 220mm	Stainless Steel EMC (retrofittable)
24563-433	6U	295mm	1	Backplane	160mm, 220mm, 280mm	Stainless Steel EMC (retrofittable)
24563-434	6U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC (retrofittable)
24563-435	6U	415mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC (retrofittable)
24563-131	3U	175mm	1	Backplane	160mm	Stainless Steel EMC (retrofittable)
24563-436	6U	475mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC (retrofittable)

Table 2/2

Katalogové číslo	Rukojeť v ceně	Mounting	Complies With	Materiál	Rack Width	Static Load
24563-132	No	Rack	IEC 60297-3-103	Hliník	84HP	11kg
24563-133	No	Rack	IEC 60297-3-103	Hliník	84HP	11kg
24563-134	No	Rack	IEC 60297-3-103	Hliník	84HP	11kg
24563-135	No	Rack	IEC 60297-3-103	Hliník	84HP	11kg
24563-136	No	Rack	IEC 60297-3-103	Hliník	84HP	11kg
24563-431	No	Rack	IEC 60297-3-103	Hliník	84HP	11kg
24563-432	No	Rack	IEC 60297-3-103	Hliník	84HP	11kg
24563-433	No	Rack	IEC 60297-3-103	Hliník	84HP	11kg
24563-434	No	Rack	IEC 60297-3-103	Hliník	84HP	11kg
24563-435	No	Rack	IEC 60297-3-103	Hliník	84HP	11kg
24563-131	No	Rack	IEC 60297-3-103	Hliník	84HP	11kg

Katalogové číslo	Rukojeť v ceně	Mounting	Complies With	Materiál	Rack Width	Static Load
24563-436	No	Rack	IEC 60297-3-103	Hliník	84HP	11kg

DALŠÍ PODROBNOSTI O PRODUKTU

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE