

# EuropacPRO 19" Subrack Kit for Railway, Shielded, EN 50155

Subrack for Railway applications, conform to EN50155 standard, shielded versions.



## VLASTNOSTI

Shock and vibration tested to EN 50155, part 12.2.11

The 19" bracket is firmly fixed to the side panel (toxic-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

The double 19" screwing position adds to additional safety (NFF standard)

IP 20, in accordance with IEC 60529

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Aluminum construction

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

|                       |                                        |
|-----------------------|----------------------------------------|
| <b>Static Load:</b>   | 15kg                                   |
| <b>Rack Width:</b>    | 84HP                                   |
| <b>Hloubka:</b>       | 235mm                                  |
| <b>Materiál:</b>      | Hliník                                 |
| <b>Complies With:</b> | IEC 60297-3-103; EN 50155 part 12.2.11 |
| <b>Product Type:</b>  | Subrack/Chassis                        |
| <b>EMC Shielding:</b> | Yes                                    |



## SPECIFIKACE

Table 1/2

| Katalogové číslo | Rack Height | Množství v balení | For Mounting | Board Depth | Gasket Type | Shock and Vibration Tolerance |
|------------------|-------------|-------------------|--------------|-------------|-------------|-------------------------------|
| 21500-079        | 3U          | 1                 | Backplane    | 220mm       | Textile EMC | 5g (force)                    |
| 21500-080        | 6U          | 1                 | Backplane    | 220mm       | Textile EMC | 5g (force)                    |

Table 2/2

| Katalogové číslo | Rukojeť v ceně | Mounting | Povrchová úprava     |
|------------------|----------------|----------|----------------------|
| 21500-079        | Yes            | Rack     | Anodized, Passivated |
| 21500-080        | Yes            | Rack     | Anodized, Passivated |

## DALŠÍ PODROBNOSTI O PRODUKTU

Test reports are available online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**