

Front Panel, Front Anodized, Rear Conductive, Unshielded

Front panel, unshielded, front anodized and rear conductive.

VLASTNOSTI

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive



Hĺoubka (D):	2.5mm
Materiál:	Hliník
Povrchová úprava:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Typ:	Front Panel without Handle



SPECIFIKACE

Table 1/3

Katalogové číslo	Rack Height	Rack Width	Množství v balení	Mounting	Front Finish	Rear Finish
30847-470	3U	2HP	1	Screw-on Front	Anodized	Conductive
30847-464	4U	63HP	1	Screw-on Front	Anodized	Conductive
30847-480	9U	8HP	1	Screw-on Front	Anodized	Conductive
30838-125	6U	5HP	1	Screw-on Front	Anodized	Conductive
30838-148	6U	28HP	1	Screw-on Front	Anodized	Conductive
30838-183	6U	63HP	1	Screw-on Front	Anodized	Conductive
30838-047	3U	8HP	1	Screw-on Front	Anodized	Conductive
30838-067	3U	28HP	1	Screw-on Front	Anodized	Conductive

Katalogové číslo	Rack Height	Rack Width	Množství v balení	Mounting	Front Finish	Rear Finish
30847-476	4U	4HP	1	Screw-on Front	Anodized	Conductive
30838-127	6U	7HP	1	Screw-on Front	Anodized	Conductive
30847-468	5U	63HP	1	Screw-on Front	Anodized	Conductive
30847-463	4U	42HP	1	Screw-on Front	Anodized	Conductive
30847-471	3U	3HP	1	Screw-on Front	Anodized	Conductive
30838-046	3U	7HP	1	Screw-on Front	Anodized	Conductive
30838-128	6U	8HP	1	Screw-on Front	Anodized	Conductive
30838-126	6U	6HP	1	Screw-on Front	Anodized	Conductive
30838-045	3U	6HP	1	Screw-on Front	Anodized	Conductive
30838-130	6U	10HP	1	Screw-on Front	Anodized	Conductive
30847-469	5U	84HP	1	Screw-on Front	Anodized	Conductive
30838-081	3U	42HP	1	Screw-on Front	Anodized	Conductive

Table 2/3

Katalogové číslo	Rack Height	Rack Width	Množství v balení	Mounting	Front Finish	Rear Finish
30838-123	3U	84HP	1	Screw-on Front	Anodized	Conductive
30847-460	2U	63HP	1	Screw-on Front	Anodized	Conductive
30838-141	6U	21HP	1	Screw-on Front	Anodized	Conductive
30847-462	4U	28HP	1	Screw-on Front	Anodized	Conductive
30838-132	6U	12HP	1	Screw-on Front	Anodized	Conductive
30838-044	3U	5HP	1	Screw-on Front	Anodized	Conductive
30838-043	3U	4HP	1	Screw-on Front	Anodized	Conductive
30838-136	6U		1	Screw-on Front	Anodized	Conductive
30838-134	6U	14HP	1	Screw-on Front	Anodized	Conductive
30838-102	3U	63HP	1	Screw-on Front	Anodized	Conductive
30847-467	5U	42HP	1	Screw-on Front	Anodized	Conductive
30838-053	3U	14HP	1	Screw-on Front	Anodized	Conductive
30847-459	2U	42HP	1	Screw-on Front	Anodized	Conductive
30847-556	9U	84HP	1	Screw-on Front	Anodized	Conductive
30847-458	2U	28HP	1	Screw-on Front	Anodized	Conductive
30838-055	3U	16HP	1	Screw-on Front	Anodized	Conductive
30838-162	6U	42HP	1	Screw-on Front	Anodized	Conductive
30838-204	6U	84HP	1	Screw-on Front	Anodized	Conductive
30847-484	9U	12HP	1	Screw-on Front	Anodized	Conductive
30847-465	4U	84HP	1	Screw-on Front	Anodized	Conductive

Table 3/3

Katalogové číslo	Rack Height	Rack Width	Množství v balení	Mounting	Front Finish	Rear Finish
30838-051	3U	12HP	1	Screw-on Front	Anodized	Conductive
30838-060	3U	21HP	1	Screw-on Front	Anodized	Conductive
30847-466	5U	28HP	1	Screw-on Front	Anodized	Conductive
30847-461	2U	84HP	1	Screw-on Front	Anodized	Conductive
30838-049	3U	10HP	1	Screw-on Front	Anodized	Conductive
30847-482	9U	10HP	1	Screw-on Front	Anodized	Conductive
30838-124	6U	4HP	1	Screw-on Front	Anodized	Conductive

Table 1/3

Katalogové číslo	Treated Edges	Complies With	EMC Shielding	Výška (H)	Šířka (W)	Certifications
30847-470	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	9.8mm	RoHS
30847-464	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	319.7mm	RoHS
30847-480	No	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	40.3mm	RoHS
30838-125	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	25mm	RoHS
30838-148	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	141.9mm	RoHS
30838-183	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	319.7mm	RoHS
30838-047	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	40.3mm	RoHS
30838-067	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	141.9mm	RoHS
30847-476	No	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	20mm	RoHS
30838-127	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	35.2mm	RoHS
30847-468	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4mm	319.7mm	
30847-463	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	213mm	RoHS
30847-471	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	14.9mm	RoHS
30838-046	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	35.2mm	RoHS

Katalogové číslo	TreatedEdges	Complies With	EMCShielding	Výška(H)	Šířka (W)	Certifications
30838-128	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	40.3mm	RoHS
30838-126	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	30.1mm	RoHS
30838-045	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	30.1mm	RoHS
30838-130	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	50.5mm	RoHS
30847-469	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4mm	426.4mm	
30838-081	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	213mm	RoHS

Table 2/3

Katalogové číslo	Treated Edges	Complies With	EMC Shielding	Výška (H)	Šířka (W)	Certifications
30838-123	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	426.4mm	RoHS
30847-460	No	IEC 60297-3-101, IEEE 1101.1/10	No	84mm	319.7mm	
30838-141	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	106.3mm	RoHS
30847-462	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	141.9mm	
30838-132	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	60.6mm	RoHS
30838-044	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	25mm	RoHS
30838-043	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	20mm	RoHS
30838-136	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	80.9mm	RoHS
30838-134	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	70.8mm	RoHS
30838-102	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	319.7mm	RoHS
30847-467	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4mm	213mm	
30838-053	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	70.8mm	RoHS



Katalogové číslo	TreatedEdges	Complies With	EMCShielding	Výška(H)	Šířka (W)	Certifications
30847-459	No	IEC 60297-3-101, IEEE 1101.1/10	No	84mm	213mm	
30847-556	No	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	426.4mm	RoHS
30847-458	No	IEC 60297-3-101, IEEE 1101.1/10	No	84mm	141.9mm	
30838-055	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	80.9mm	RoHS
30838-162	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	213mm	RoHS
30838-204	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	426.4mm	RoHS
30847-484	No	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	60.6mm	RoHS
30847-465	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	426.4mm	RoHS

Table 3/3

Katalogové číslo	Treated Edges	Complies With	EMC Shielding	Výška (H)	Šířka (W)	Certifications
30838-051	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	60.6mm	RoHS
30838-060	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	106.3mm	RoHS
30847-466	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4mm	141.9mm	
30847-461	No	IEC 60297-3-101, IEEE 1101.1/10	No	84mm	426.4mm	RoHS
30838-049	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	50.5mm	RoHS
30847-482	No	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	50.5mm	RoHS
30838-124	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	20mm	RoHS

DALŠÍ PODROBNOSTI O PRODUKTU

Please order fixing material (sleeves, collar screws) separately.



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE