

Guide Rail With Coding for CompactPCI/ VME64x, PC



New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

VLASTNOSTI

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to a optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

Optional ESD clip for an conductive contact between PCB and horizontal rail available

Storage temperature: from -40 °C ... 130 °C

Works With:	Subracks; Cases; 19" Chassis; Systems
Typ:	Coding
Produktová řada:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac
Product Type:	Guide Rail



SPECIFIKACE

Katalogové číslo	Materiál	Barva	Množství v balení	Board Depth	Groove Width	Complies With	Povrchová úprava
64568-110	Fiber-Reinforced Plastic, Hliník	Grey, Silver	1	160mm	2.5	EN 45545-2	
64568-085	Fiber-Reinforced Plastic	Red	1	70mm	2	EN 45545-2	
64568-112	Fiber-Reinforced Plastic, Hliník	Grey, Silver	1	220mm	2.5	EN 45545-2	
64568-111	Fiber-Reinforced Plastic, Hliník	Red, Silver	1	220mm	2.5	EN 45545-2	
64568-086	Fiber-Reinforced Plastic	Grey	1	70mm	2	EN 45545-2	
64568-109	Fiber-Reinforced Plastic, Hliník	Red, Silver	1	160mm	2.5	EN 45545-2	
64568-091	Fiber-Reinforced Plastic	Red	1	220mm	2	EN 45545-2	
64568-090	Fiber-Reinforced Plastic	Grey	1	160mm	2	EN 45545-2	
64568-092	Fiber-Reinforced Plastic	Grey	1	220mm	2	EN 45545-2	
64568-089	Fiber-Reinforced Plastic	Red	1	160mm	2	EN 45545-2	
24568-360	Fiber-Reinforced Plastic	Grey	10	70mm	2	EN 45545-2	
24568-358	Fiber-Reinforced Plastic	Grey	10	160mm	2	EN 45545-2	
24568-357	Fiber-Reinforced Plastic	Red	10	70mm	2	EN 45545-2	
24568-356	Fiber-Reinforced Plastic	Red	10	160mm	2	EN 45545-2	
24568-332	Fiber-Reinforced Plastic, Hliník	Red, Silver	10	340mm	2.5	EN 45545-2	Anodized
24568-331	Fiber-Reinforced Plastic, Hliník	Red, Silver	10	280mm	2.5	EN 45545-2	Anodized
24568-341	Fiber-Reinforced Plastic, Hliník	Grey, Silver	10	280mm	2.5	EN 45545-2	Anodized
24568-342	Fiber-Reinforced Plastic, Hliník	Grey, Silver	10	340mm	2.5	EN 45545-2	

DALŠÍ PODROBNOSTI O PRODUKTU

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE