


Mounting Plate for 19" Case and Subrack



Mounting plate for heavy components or proprietary electronic assemblies. Suitable for RatiopacPRO/-AIR, CompacPRO and EuropacPRO.

Guide rails Type 4,4" and type strengthened cannot be used in combination with a mounting plate. Top / bottom cover which will be inserted into the groove of the light (type L) horizontal rails cannot be used in combination with a mounting plate.

VLASTNOSTI

For assembly of heavy components

Mounting plate, full width: The mounting plate is as wide as the subrack/system case and is fixed to the side panels

Mounting plate, partial width: The partial width mounting plate fixed to the side panel by means of an assembly strip

The chassis plate can't be combined with EMC top- / bottom covers

Materiál: Hliník
Product Type: Mounting Plate
Works With: Subracks



SPECIFIKACE

Katalogové číslo	Rack Width	Množství v balení	Hloubka	Produktová řada	Šířka	Certifikations
34562-750	42HP	1	172.5m m	EuropacPRO, CompacPRO, RatiopacPRO, PropacPRO	217.99m m	RoHS
34562-759	63HP	1	292.2m m	EuropacPRO, RatiopacPRO, CompacPRO	324.67m m	RoHS
34562-752	84HP	1	172.5m m	EuropacPRO, CompacPRO, RatiopacPRO, PropacPRO	431.35m m	RoHS
34562-755	63HP	1	232.5m m	EuropacPRO, RatiopacPRO, CompacPRO	324.67m m	RoHS
34562-758	42HP	1	292.2m m	EuropacPRO, RatiopacPRO, CompacPRO	217.99m m	RoHS
34562-870	84HP	1	352.5m m	EuropacPRO	431.35m m	

Katalogové číslo	Rack Width	Množství v balení	Hloubka	Produktová řada	Šířka	Certifikace
34562-748	84HP	1	112.5m m	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	324.67m m	RoHS
34562-747	63HP	1	112.5m m	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	324.67m m	RoHS
34562-754	42HP	1	232.5m m	EuropacPRO, RatiopacPRO, CompacPRO	217.99m m	RoHS
34562-871	84HP	1	412.5m m	EuropacPRO	431.35m m	
34562-756	84HP	1	232.5m m	EuropacPRO, RatiopacPRO, CompacPRO	431.35m m	RoHS
34562-751	63HP	1	172.5m m	EuropacPRO, RatiopacPRO, CompacPRO, PropacPRO	324.67m m	RoHS
34562-760	84HP	1	292.5m m	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	431.35m m	RoHS
34562-746	42HP	1	112.5m m	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	217.99m m	RoHS
34562-745	28HP	1	112.5m m	EuropacPRO, RatiopacPRO, CompacPRO	146.88m m	RoHS
34562-753	28HP	1	232.5m m	EuropacPRO, RatiopacPRO, CompacPRO	146.88m m	RoHS
34562-757	28HP	1	292.2m m	EuropacPRO, RatiopacPRO, CompacPRO	146.88m m	RoHS
34562-749	28HP	1	172.5m m	EuropacPRO, RatiopacPRO, CompacPRO	146.88m m	RoHS

DALŠÍ PODROBNOSTI O PRODUKTU

Please order assembly kit for mounting plate separately.

Other versions on request.

Fixing strips required for partial width, please order separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE