

RatiopacPRO EMC Front Panel, Slotted, Shielded



The EMC front panel can be inserted in special horizontal rails with an elevation. No screws are needed for the fixing. The design enable a users to use a front foil.

VLASTNOSTI

Fixing does not require screws

Special horizontal rails cover the edges of the front panel (top and bottom) and prevent bowing of the front panel

Materiál: Hliník
Povrchová úprava: Anodized; Passivated
Accessory Type: Front panel
Product Type: Front Panel



SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Rack Width	Množství v balení	Front Finish	Rear Finish	Treated Edges
24572-609	4U	63HP	1	Anodized	Conductive	No
24572-610	4U	84HP	1	Anodized	Conductive	No
24572-604	3U	42HP	1	Anodized	Conductive	No
24572-599	2U	28HP	1	Anodized	Conductive	No
24572-607	4U	28HP	1	Anodized	Conductive	No
24572-600	2U	42HP	1	Anodized	Conductive	No
24572-601	2U	63HP	1	Anodized	Conductive	No
24572-605	3U	63HP	1	Anodized	Conductive	No
24572-602	2U	84HP	1	Anodized	Conductive	No
24572-603	3U	28HP	1	Anodized	Conductive	No
24572-608	4U	42HP	1	Anodized	Conductive	No

Katalogové číslo	Rack Height	Rack Width	Množství v balení	Front Finish	Rear Finish	Treated Edges
24572-606	3U	84HP	1	Anodized	Conductive	No

Table 2/2

Katalogové číslo	Hloubka	Výška	Šířka
24572-609	2.5mm	172.9mm	319.7mm
24572-610	2.5mm	172.9mm	426.4mm
24572-604	2.5mm	128.4mm	213.2mm
24572-599	2.5mm	84mm	141.9mm
24572-607	2.5mm	172.9mm	141.9mm
24572-600	2.5mm	84mm	213.2mm
24572-601	2.5mm	84mm	319.7mm
24572-605	2.5mm	128.4mm	319.7mm
24572-602	2.5mm	84mm	426.4mm
24572-603	2.5mm	128.4mm	141.9mm
24572-608	2.5mm	172.9mm	213.2mm
24572-606	2.5mm	128.4mm	426.4mm

DALŠÍ PODROBNOSTI O PRODUKTU

To obtain a shielded case, all EMC sealings must be fitted (front panel/rear panel - side panel; side panel - cover plate; front panel/rear panel - horizontal rail; horizontal rail - horizontal rail).

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE