

Partielle døre | Gulvskabe, DP

Deldøre giver mulighed for mange forskellige og lettilgængelige konfigurationer af adskilte rum inde i skabet.



FUNKTIONER

Beskrivelse: Til inddeling af skabsfronten i sektioner ved brug af CDH og CDHK vandret deleskinne. Udstyret med dobbelt-bit 3 mm lås (op til 400 mm = 1 lås, over 400 mm = 2 låse).

Materiale: 1.75 mm stålplade.

Overfladebehandling: Strukturpulvermaling. RAL 7035.

Tæthedsgrad: IP 44.

Pakke størrelse: 1 dør med hængsler, låse og monteringsmateriale.

Monteringskrav: Tilføj CDH for MC rammer og brug CDHK til MK rammer. Brug DPC/DPCV til top- og bundpaneler.

Farve:	Light Gray
Materiale:	Lakeret Stål
Finish:	Struktur Pulvermaling
Farvekode:	RAL 7035

SPECIFIKATIONER

Table 1/2

Katalognummer	Højde	Bredde	Dybde	Produktfamilie	Enclosure Material
DP01506R5	150mm	600mm	17mm	Free-Standing	Lakeret Stål
DP10008R5	1000mm	800mm	17mm	Free-Standing	Lakeret Stål

Katalognummer	Højde	Bredde	Dybde	Produktfamilie	Enclosure Material
DP03006R5	300mm	600mm	17mm	Free-Standing	Lakeret Stål
DP02506R5	250mm	600mm	17mm	Free-Standing	Lakeret Stål
DP01508R5	150mm	800mm	17mm	Free-Standing	Lakeret Stål
DP04006R5	400mm	600mm	17mm	Free-Standing	Lakeret Stål
DP05006R5	500mm	600mm	17mm	Free-Standing	Lakeret Stål
DP02004R5	200mm	400mm	17mm	Free-Standing	Lakeret Stål
DP06008R5	600mm	800mm	17mm	Free-Standing	Lakeret Stål
DP12006R5	1200mm	600mm	17mm	Free-Standing	Lakeret Stål
DP06004R5	600mm	400mm	17mm	Free-Standing	Lakeret Stål
DP08006R5	800mm	600mm	17mm	Free-Standing	Lakeret Stål
DP02504R5	250mm	400mm	17mm	Free-Standing	Lakeret Stål
DP04004R5	400mm	400mm	17mm	Free-Standing	Lakeret Stål
DP05004R5	500mm	400mm	17mm	Free-Standing	Lakeret Stål
DP03008R5	300mm	800mm	17mm	Free-Standing	Lakeret Stål
DP10006R5	1000mm	600mm	17mm	Free-Standing	Lakeret Stål
DP02008R5	200mm	800mm	17mm	Free-Standing	Lakeret Stål
DP08008R5	800mm	800mm	17mm	Free-Standing	Lakeret Stål
DP02006R5	200mm	600mm	17mm	Free-Standing	Lakeret Stål

Table 2/2

Katalognummer	Højde	Bredde	Dybde	Produktfamilie	Enclosure Material
DP03004R5	300mm	400mm	17mm	Free-Standing	Lakeret Stål
DP01504R5	150mm	400mm	17mm	Free-Standing	Lakeret Stål
DP12008R5	1200mm	800mm	17mm	Free-Standing	Lakeret Stål
DP02508R5	250mm	800mm	17mm	Free-Standing	Lakeret Stål
DP05008R5	500mm	800mm	17mm	Free-Standing	Lakeret Stål
DP04008R5	400mm	800mm	17mm	Free-Standing	Lakeret Stål
DP06006R5	600mm	600mm	17mm	Free-Standing	Lakeret Stål

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE