

HFF Steel Nailing Plate



The HFF nailing plate is sold separately from the A12 couplers. The plates easily attach to the couplers by orienting the hexagon opening in the plate to the coupler and then rotating the plate 15 degrees.

Used in segmental pour and closure pour applications. Permanent form saving plates allow easy attachment to form work, eliminating costly damage to the forms.

FUNKTIONER

Designed for use with the A12 coupler families

Positively locks onto the hexagon-shaped coupler

Easy to install

No special tools required

Materiale: Spring Steel

SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Length (L)	Hex Width (W)
EL1820HFF	152860	18 mm, 20 mm	#6	20M	50mm	27 mm
EL2225HFF	154420	22 mm, 25 mm	#7, #8	25M	70mm	36 mm
EL1012HFF	152840	10 mm, 12 mm	#3, #4	10M	50mm	17 mm
EL1416HFF	152850	14 mm, 16 mm	#5	15M	50mm	22 mm

Table 2/2


Katalognummer	Artikelnummer	Height (H)	Pakke mængde
EL1820HFF	152860	5 mm	100
EL2225HFF	154420	5 mm	75
EL1012HFF	152840	5 mm	100
EL1416HFF	152850	5 mm	100

YDERLIGERE PRODUKTOPLYSNINGER

Can also be used on A2N couplers.

Always wear gloves when installing plates to couplers.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE