

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 63 HP



Combinations of horizontal rails and side panels

*+ can be combined, - = combination not recommended

	Light rail	Standard rail	Rugged rail	Rugged rail with 3-hole fixing
Standard rail	-	+	+	+
Standard rail with 3-hole fixing	+	+	+	+
Rugged rail	+	+	-	-
Rugged rail with 3-hole fixing	+	+	-	-

Light rail: 1. Standard rail: 2. Rugged rail: 3. Rugged rail with 3-hole fixing: 4.

KATALOGNUMMER

34566-263

The rugged horizontal rail type can handle shock and vibration up to 25 g.

FUNKTIONER

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings



PRODUKTEGENSKABER

Rack Width: 63HP

Pakke mængde: 1

Finish: Anodized

Length: 325.12mm

Materiale: Aluminium

Produktfamilie: EuropacPRO

Product Type: Horizontal Rail

Type: Rugged, KD

Works With: Subracks

Net Weight: 0.2kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YDERLIGERE PRODUKTOPLYSNINGER

Without M4 thread to front, without printing and without notch for 19" bracket.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE