

EuropacPRO 19" Subrack Kit for Railway, Shielded, EN 50155

Subrack for Railway applications, conform to EN50155 standard, shielded versions.



FUNKTIONER

Shock and vibration tested to EN 50155, part 12.2.11

The 19" bracket is firmly fixed to the side panel (toxic-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

The double 19" screwing position adds to additional safety (NFF standard)

IP 20, in accordance with IEC 60529

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Aluminum construction

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Static Load:	15kg
Rack Width:	84HP
Dybde:	235mm
Materiale:	Aluminium
Complies With:	IEC 60297-3-103; EN 50155 part 12.2.11
Product Type:	Subrack/Chassis
EMC Shielding:	Yes



SPECIFIKATIONER

Table 1/2

Katalognummer	Rack Height	Pakke mængde	For Mounting	Board Depth	Gasket Type	Shock and Vibration Tolerance
21500-079	3U	1	Backplane	220mm	Textile EMC	5g (force)
21500-080	6U	1	Backplane	220mm	Textile EMC	5g (force)

Table 2/2

Katalognummer	Håndtag inkluderet	Mounting	Finish
21500-079	Yes	Rack	Anodized, Passivated
21500-080	Yes	Rack	Anodized, Passivated

YDERLIGERE PRODUKTOPLYSNINGER

Test reports are available online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE