

EuropacPRO Cover Plate for Bolting to Rugged Side Panel



A cover plate is used for electromagnetic shielding or as mechanical protection.

FUNKTIONER

Perforation degree 58%

Rack Width:	84HP
Materiale:	Aluminium
Product Type:	Cover Plate
Produktfamilie:	EuropacPRO
Finish:	Passivated
Type:	Perforated
Works With:	Subracks



SPECIFIKATIONER

Katalognummer	Dybde	Pakke mængde	Pakkeenhed	Torque
24568-004	175mm	2	Pair	2.1N·m
24568-036	277.75mm	2	Pair	2.1N·m
24568-032	275mm	2	Pair	2.1N·m
24568-020	355mm	2	Pair	2.1N·m
24568-016	295mm	2	Pair	2.1N·m
24568-012	295mm	2	Pair	2.1N·m
24568-008	235mm	2	Pair	2.1N·m

YDERLIGERE PRODUKTOPLYSNINGER

A top cover locking mechanism is optionally available that also fixes the top cover in the front and rear guide rail.

4 stainless steel EMC contact strips per subrack are required for shielding, please order separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE