

Quick Release Fastener

1/4 rotary lock with defined stop.

FUNKTIONER

1/4 rotary lock with defined stop

Identification of locking position due to slot position

Vibration and shake proof

Qty 100 pieces

Works With: Front Panels
Product Type: Hardware Kit
Finish: Nickel Plated
Materiale: Stål; Zinc Alloy; Thermoplastic



SPECIFIKATIONER

Katalognummer	Farve	Pakke mængde	Farvekode	Dybde	Højde	Bredde	Fastener Type
21101-850	Jet Black	100	RAL 9005	20.6mm	6mm	7mm	Knurled, Slotted Head
21101-847	Pebble Grey	100	RAL 7032	16.7mm	6mm	7mm	Slotted Head
21101-849	Pebble Grey	100	RAL 7032	20.6mm	6mm	7mm	Knurled, Slotted Head
21101-848	Jet Black	100	RAL 9005	16.7mm	6mm	7mm	Slotted Head

YDERLIGERE PRODUKTOPLYSNINGER

Quick-release fasteners: mounting without threaded inserts.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE