

Rack Safety Plus, 3 U, 208 / 240 V AC



FUNKTIONER

19", 3 U Power Distribution Unit with Emergency Stop function

Supplies AC mains power to electrical or electronic devices as a central power switch

208 V phase to phase or phase to neutral or 240 V phase to phase mains input

AC outputs with different connector types, switched by ON/OFF switch

Permanent AC Outputs (Service)

All outputs are protected by circuit breakers

The emergency stop function meets the requirements of EN 60947-5-1 and EN 60204-1 and is vandalism-proof

An additional external emergency stop push button can be connected to the system

UL pending

Function:	Emergency Stop
Inrush Current Limiter:	No
Residual Current Device:	No
Circuit Breaker Cover:	No
Works With:	Varistar CP; Novastar
Accessory Type:	Power distribution accessories

SPECIFIKATIONER

Table 1/2

Katalognummer	Product Type	Indgangsspænding AC	Antal faser	EMC Filter	Surge Arrester	Rack Height
21272-003	Power Distributor	208 – 240V	1	No	No	3U
21272-001	Power Distributor	208 – 240V	1	Yes	Yes	3U

Table 2/2

Katalognummer	Stiktype	Pakke mængde
21272-003	IEC C13 lockable	1
21272-001	IEC C13, IEC C19	1

YDERLIGERE PRODUKTOPLYSNINGER

For exact configuration of optional features and example configuration please refer to the item(s) delivered table.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE