

Rack Safety Plus, 3 U, 230 / 400 V AC

The nVent SCHROFF Rack Safety Plus unit is a 19" power distribution unit used to supply AC mains power to electrical or electronic devices as a central power switch. In addition it is equipped with an emergency stop function.

FUNKTIONER

19", 3 U Power Distribution Unit with Emergency Stop function

Supplies AC mains power to electrical or electronic devices as a central power switch

400 V 3-phase or 230 V 1-phase mains input with mains fuses

AC outputs with different connector types, switched by ON/OFF switch

Permanent AC Outputs (Service)

All outputs are protected by circuit breakers

The emergency stop function meets the requirements of EN 60947-5-1 and EN 60204-1 and is vandalism-proof

An additional external emergency stop push button can be connected to the system



Function:	Emergency Stop
Works With:	Varistar CP; Novastar
Accessory Type:	Power distribution accessories
Residual Current Device:	Yes



SPECIFIKATIONER

Table 1/2

Katalognummer	Product Type	Indgangsspænding AC	Antal faser	EMC Filter	Surge Arrester	Inrush Current Limiter
21270-010	Power Distributor	230V	1	No	Yes	Yes
21270-011	Power Distributor	230V	1	No	No	No
21270-005	Power Distributor	230V	1	No	Yes	No

Katalognummer	Product Type	Indgangsspænding AC	Antalfaser	EMCFilter	Surge Arrester	Inrush Current Limiter
21270-003	Power Distributor	230V	1	No	No	No
21270-012	Power Distributor	400V	3	No	No	No
21270-001	Power Distributor	400V	3	Yes	Yes	Yes

Table 2/2				
Katalognummer	Circuit Breaker Cover	Rack Height	Stiktype	Pakke mængde
21270-010	Yes	3U	IEC C13	1
21270-011	No	3U	SCHUKO, IEC C13	1
21270-005	Yes	3U	SCHUKO	1
21270-003	No	3U	IEC C13	1
21270-012	No	3U	IEC C13, IEC C13 LOCK	1
21270-001	Yes	3U	SCHUKO, IEC C13	1

YDERLIGERE PRODUKTOPLYSNINGER

For exact configuration of optional features and example configuration please refer to the item(s) delivered table.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE