

Heizgeräte für Gefahrenbereiche, DAHHL



Designed for hazardous locations where electronic components require protection from cold freezing temperatures, condensation and corrosion.

INDUSTRIE-STANDARDS

ATEX, IECEx
 II2G Ex d IIC T3 / II2 D Ex Td A21 IP65 T200 C
 NEC CSA us
 Class I, Div 1 Groups A, B, C, D / Class II Div 1 Groups E, F, G

MERKMALE

50W, 80W, 200W, 300W, 400W and 600W models available

Provides freeze protection down to -76 F / -60 C

Conductive and Convection heating types available

50W and 80W models can be mounted directly to manifolds, measuring or analyzing instruments, control valves, and similar equipment

200W, 300W, 400W, 600W models are finned heaters that heat the area by transferring the heat from the heater to surrounding air, creating a convection current

Two thermostat options available with a 50 F / 10 C or 68 F / 20 C set point

Material: Aluminium
Oberfläche: Eloxiert
Farbe: Schwarz

SPEZIFIKATIONEN

Katalognummer	Höhe	Breite	Tiefe	Nennspannung	Heizleistung	Spannung AC
HLTSTAT10C	28mm	23mm	109mm			
HLTSTAT20C	28mm	23mm	109mm			
DAHHL501AC	89mm	41mm	30mm	115V	50W	110V
DAHHL801AC	89mm	41mm	30mm	115V	80W	110V

Katalognummer	Höhe	Breite	Tiefe	Nennspannung	Heizleistung	Spannung AC
DAHHL4001A	226mm	229mm	61mm	115V	400W	110V
DAHHL6001A	325mm	229mm	61mm	115V	600W	110V
DAHHL6002A	325mm	229mm	61mm	220V	600W	207V
DAHHL4002A	226mm	229mm	61mm	220V	400W	207V
DAHHL300AC	325mm	229mm	61mm	115V	300W	110V
DAHHL200AC	226mm	229mm	61mm	115V	200W	110V

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE