

Full Height Swing Frames, ESFC

A swing frame for 19" equipment that provides additional mounting space for such equipment, as well as rear access to the fitted components and equipment once opened.



FEATURES

Description: Full height swing frame for 19" components allowing left and right hand opening. Can be used in steel, combinable and compact enclosures. Hinges designed to give extra build-in depth. Adjustable top hinge for square mounting of the swing frame. Rigid W-shaped frame profile for heavy equipment. Zinc plated 19" vertical profiles for direct earthing of the mounted components. Standard equipped with 130° hinges. Can also be mounted on the side of 600 mm deep floor standing enclosures. For steel, combinable enclosures use transversal support bars ESFB in combination with VBD if required. Adjustable in depth by steps of 12.5 mm.

Maximum load: 1800N, supplied with a self positioning device.

Lock: Two 3 mm double-bit locks.

Material: 19" vertical profiles 2 mm zinc plated steel. Frame: vertical profiles 2 mm and horizontal profiles 3 mm.

Pack quantity: 1 swing frame with hinges.

Mounting requirements: ESFC for 600 mm, 800 mm, 1000 mm, 1200 mm wide steel, combinable enclosures. Add ESFB for mounting in a steel, combinable enclosure.

Thickness: 2mm
Material: Mild Steel
Finish: Zinc Plated

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Rack Units	Enclosure Material
ESFC316	ESFC316	1600mm	499mm	80mm	31U	Mild Steel

Catalog Number	Article Number	Height	Width	Depth	Rack Units	Enclosure Material
ESFC456	ESFC456	2200mm	499mm	80mm	45U	Mild Steel
ESFC406	ESFC406	2000mm	499mm	80mm	40U	Mild Steel
ESFC276	ESFC276	1400mm	499mm	80mm	27U	Mild Steel
ESFC366	ESFC366	1800mm	499mm	80mm	36U	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE