

Lifting Eye Bolts, LE

These lifting eyes guarantee safe transportation and handling of the enclosure.

FEATURES

Description: Mounts directly to the frame corner pieces of the enclosure for when lifting operations are required.

Complies with DIN 580 lifting requirements. M12 thread.

Maximum load: 3400N per lifting eye with max angle of 45°. Please follow nVent HOFFMAN lifting instructions.

Pack quantity: 4 pieces.



SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
LE9304	LE9304	71mm	50mm	30mm	Mild Steel	Zinc Plated
LE9304SS	LE9304SS	71mm	50mm	30mm	Stainless Steel 304	Mill
LE9316SS		71mm	50mm	30mm	Stainless Steel 316L	Mill

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.