


Rail Surge Plane Strip Busbar



FEATURES

Meets AREMA® recommended design criteria

Improved low impedance busbar

Design assistance available for special applications

Available in bare or tinned versions

Material: Electrolytic Copper

SPECIFICATIONS

Catalog Number	Finish	Height (H)	Width (W)	Thickness (T)	Slot Size (SS)	Hole Size 1 (HS1)	Hole Size 2 (HS2)
B2700HC60	Bare	1524 mm	50.8 mm	1.6 mm	12.7 x 15.9 mm	7.9 mm	9.5 mm
B2700HC36T	Tinned	914.4 mm	50.8 mm	1.6 mm	12.7 x 15.9 mm	7.9 mm	9.5 mm
B2700HC60T	Tinned	1524 mm	50.8 mm	1.6 mm	12.7 x 15.9 mm	7.9 mm	9.5 mm
B2700HC14T	Tinned	355.6 mm	50.8 mm	1.6 mm	12.7 x 15.9 mm	7.9 mm	9.5 mm
B2700HC72	Bare	1828.8 mm	50.8 mm	1.6 mm	12.7 x 15.9 mm	7.9 mm	9.5 mm
B2700HC72T	Tinned	1828.8 mm	50.8 mm	1.6 mm	12.7 x 15.9 mm	7.9 mm	9.5 mm
B2700HC48T	Tinned	1219.2 mm	50.8 mm	1.6 mm	12.7 x 15.9 mm	7.9 mm	9.5 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE