

19" Front Panel for Thermostat With Digital Display, 1 U



19" Front Panel for Thermostat With Digital Display, 1 U

FEATURES

19" Front Panel, 1 U, with cut-out for thermostat with digital display

Accessory Type: Front panel



SPECIFICATIONS

Table 1/3

Catalog Number	Type	Mounting	EMC Shielding	Material	Front Finish	Rear Finish
30118-315	19" Front Panel	Screw-on Front	No	Aluminum	Painted	Painted
30118-267	19" Front Panel	Screw-on Front	No	Aluminum	Anodized	Anodized
30118-360	19" Front Panel	Screw-on Front	No	Aluminum	Painted	Painted

Table 2/3

Catalog Number	Color Code	Rack Height	Height	Rack Width	Width	Depth
30118-315	RAL 7035	1U	43mm	95HP	483mm	3mm
30118-267		1U	35mm		76mm	3mm
30118-360	RAL 7021	1U	43mm	95HP	483mm	3mm

Table 3/3

Catalog Number	Package Quantity	Finish
30118-315	1	Powder Coated

Catalog Number	Package Quantity	Finish
30118-267	1	Anodized
30118-360	1	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE