

# Collar Screw, Knurled Head Short Version



Integrated load spreading, replaces separate washer.  
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

## FEATURES

For assembly of partial width front panels

For EuropacPRO and RatiopacPRO

Knurled head for manual screwing / unscrewing

**Works With:** Front Panels  
**Type:** Screw  
**Product Type:** Screw



## SPECIFICATIONS

Table 1/2

| Catalog Number | Length | Material         | Finish        | Package Quantity | Thread Size | Depth  |
|----------------|--------|------------------|---------------|------------------|-------------|--------|
| 21101-749      | 12.3mm | Brass, Lead Free | Nickel Plated | 100              | M2.5        | 18.3mm |
| 21101-106      | 11mm   | Steel            |               |                  | M2.5        |        |
| 21100-268      | 11mm   | Brass            | Nickel Plated | 100              | M2.5        |        |

Table 2/2

| Catalog Number | Height | Width | Torque | Certifications |
|----------------|--------|-------|--------|----------------|
| 21101-749      | 8mm    | 8mm   | 0.3N·m | RoHS           |
| 21101-106      |        |       |        |                |
| 21100-268      |        |       |        |                |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**