

EuropacPRO Perforated Rail for Connector



Perforated flat rail for connector mounting i.a.w. EN 60603-2 and DIN 41612, on VT horizontal rails.

FEATURES

In conjunction with rear horizontal rails, VT

For Connector Mounting in accordance with EN 60603-2, DIN 41612

Material: Aluminum
Finish: Passivated
Product Type: Perforated Rail



SPECIFICATIONS

Catalog Number	Rack Width	Package Quantity	Length	Product Family	Works With	Certifications
20822-052	4HP	4	20.32m m	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	
20822-046	40HP	4	203.2m m	EuropacPRO	Subracks	RoHS
20822-053	8HP	4	40.64m m	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	
20822-051	20HP	4	101.6m m	EuropacPRO	Subracks	RoHS
20822-047	60HP	4	304.8m m	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	RoHS
20822-050	42HP	4	213.36m m	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	RoHS
20822-049	28HP	4	142.24m m	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	RoHS

Catalog Number	Rack Width	Package Quantity	Length	Product Family	Works With	Certifications
20822-048	84HP	4	431.8m m	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	RoHS

ADDITIONAL PRODUCT DETAILS

A threaded insert is required to secure the perforated rail on the horizontal rail.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE