

# Front Handle, Retrofitting for RatiopacPRO

With this front handle the flexible and robust RatiopacPRO/-AIR case, is simple to convert for easier handling.

## FEATURES

For retrofitting of cases with cover strip and replace it by a front handle

**Material:** Aluminum  
**Product Type:** Handle



## SPECIFICATIONS

Table 1/2

| Catalog Number | Package Quantity | Handle Type  | Color | Finish        | Product Family  | Type   |
|----------------|------------------|--------------|-------|---------------|-----------------|--------|
| 24571-302      | 2                | Front Handle | Grey  | Powder Coated | RatiopacPRO     | Static |
| 24571-303      | 2                | Front Handle | Grey  | Powder Coated | RatiopacPRO     | Static |
| 24572-708      | 2                |              |       | Powder Coated |                 |        |
| 24571-304      | 2                | Front Handle | Grey  | Powder Coated | RatiopacPRO AIR | Static |
| 24571-305      | 2                | Front Handle | Grey  | Powder Coated | RatiopacPRO AIR | Static |
| 24571-306      | 2                | Front Handle | Grey  | Powder Coated | RatiopacPRO AIR | Static |
| 24571-301      | 2                | Front Handle | Grey  | Powder Coated | RatiopacPRO     | Static |
| 24571-993      | 2                | Front Handle | Grey  | Powder Coated | RatiopacPRO     | Static |

Table 2/2

| Catalog Number | Works With             | Certifications |
|----------------|------------------------|----------------|
| 24571-302      | Cases, RatiopacPRO     | RoHS           |
| 24571-303      | Cases, RatiopacPRO     | RoHS           |
| 24572-708      | Cases, RatiopacPRO     |                |
| 24571-304      | Cases, RatiopacPRO AIR | RoHS           |
| 24571-305      | Cases                  | RoHS           |
| 24571-306      | Cases                  | RoHS           |
| 24571-301      | Cases, RatiopacPRO     | RoHS           |
| 24571-993      | Cases, RatiopacPRO     | RoHS           |

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**