

Varistar CP Seismic Heavy Load Cabinet, Bellcore Zone 4, EMC, 2100H 600W 600D

CATALOG NUMBER

10630-048

Cabinet with IP 55 and EMC compliance for extreme seismic environments tested to Bellcore zone 4 with a dynamic load-carrying capacity of 500 kg. Customised solutions with higher loading are available. The cabinet is widely used in ICT applications in earthquake prone areas, Construction and Shipping Facilities, Airports, Railways and many more.

Other dimensions and versions can be configured on the Online Configurator

FEATURES

Earthquake secure up to Bellcore Zone 4, tested with 500 KGs per Telcordia GR-63 Core, NEBS Certified

Static load-carrying capacity 1600 kg

Type of Protection IP55

High Shielding capability tested per IEC 61587-3, with EN45545-2 Fire safety gasket



PRODUCT ATTRIBUTES

Product Type: Cabinet

Product Family: Varistar CP

Frame Material: Steel

Finish: Powder Coated

Rack Height: 42U

Height: 2000mm

Width: 600mm

Depth: 600mm

Static Load: 1600kg

Protection Rating: IP55

Complies With: IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-3; IEC 61587-1; IEC 61587-2; EN 45545-2; Telcordia GR-63 Core Zone 4

Color: Black Grey

Color Code: RAL 7021

Frequency: 50 Hz

Material: Steel

Net Weight: 180.164kg

Package Quantity: 1

Shock and Vibration Tolerance: 5g (force)

Works With: Varistar CP

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE