

# Partial Doors For Floor Standing Enclosures, DP

Partial doors allow for many different, easily accessible configurations of separate compartments, within the enclosure.



## FEATURES

**Description:** To divide the enclosure front into sections when used in conjunction with the horizontal divider CDH/CHDK. Equipped with double-bit 3 mm lock (1 lock up to 400 mm, over 400 mm height 2 locks).

**Material:** 1.75 mm steel plate.

**Finish:** RAL 7035 structured powder coating.

**Protection:** Complies with IP 44.

**Pack quantity:** 1 door with hinges, locks and mounting accessories.

**Mounting requirements:** Add CDH for MC frames and use CDHK for MK frames. Use DPC/DPCV for top and bottom panels.

**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

## SPECIFICATIONS

Table 1/2

| Catalog Number | Height | Width | Depth | Product Family | Enclosure Material |
|----------------|--------|-------|-------|----------------|--------------------|
| DP01506R5      | 150mm  | 600mm | 17mm  | Free-Standing  | Mild Steel         |
| DP10008R5      | 1000mm | 800mm | 17mm  | Free-Standing  | Mild Steel         |

| Catalog Number | Height | Width | Depth | Product Family | Enclosure Material |
|----------------|--------|-------|-------|----------------|--------------------|
| DP03006R5      | 300mm  | 600mm | 17mm  | Free-Standing  | Mild Steel         |
| DP02506R5      | 250mm  | 600mm | 17mm  | Free-Standing  | Mild Steel         |
| DP01508R5      | 150mm  | 800mm | 17mm  | Free-Standing  | Mild Steel         |
| DP04006R5      | 400mm  | 600mm | 17mm  | Free-Standing  | Mild Steel         |
| DP05006R5      | 500mm  | 600mm | 17mm  | Free-Standing  | Mild Steel         |
| DP02004R5      | 200mm  | 400mm | 17mm  | Free-Standing  | Mild Steel         |
| DP06008R5      | 600mm  | 800mm | 17mm  | Free-Standing  | Mild Steel         |
| DP12006R5      | 1200mm | 600mm | 17mm  | Free-Standing  | Mild Steel         |
| DP06004R5      | 600mm  | 400mm | 17mm  | Free-Standing  | Mild Steel         |
| DP08006R5      | 800mm  | 600mm | 17mm  | Free-Standing  | Mild Steel         |
| DP02504R5      | 250mm  | 400mm | 17mm  | Free-Standing  | Mild Steel         |
| DP04004R5      | 400mm  | 400mm | 17mm  | Free-Standing  | Mild Steel         |
| DP05004R5      | 500mm  | 400mm | 17mm  | Free-Standing  | Mild Steel         |
| DP03008R5      | 300mm  | 800mm | 17mm  | Free-Standing  | Mild Steel         |
| DP10006R5      | 1000mm | 600mm | 17mm  | Free-Standing  | Mild Steel         |
| DP02008R5      | 200mm  | 800mm | 17mm  | Free-Standing  | Mild Steel         |
| DP08008R5      | 800mm  | 800mm | 17mm  | Free-Standing  | Mild Steel         |
| DP02006R5      | 200mm  | 600mm | 17mm  | Free-Standing  | Mild Steel         |

Table 2/2

| Catalog Number | Height | Width | Depth | Product Family | Enclosure Material |
|----------------|--------|-------|-------|----------------|--------------------|
| DP03004R5      | 300mm  | 400mm | 17mm  | Free-Standing  | Mild Steel         |
| DP01504R5      | 150mm  | 400mm | 17mm  | Free-Standing  | Mild Steel         |
| DP12008R5      | 1200mm | 800mm | 17mm  | Free-Standing  | Mild Steel         |
| DP02508R5      | 250mm  | 800mm | 17mm  | Free-Standing  | Mild Steel         |
| DP05008R5      | 500mm  | 800mm | 17mm  | Free-Standing  | Mild Steel         |
| DP04008R5      | 400mm  | 800mm | 17mm  | Free-Standing  | Mild Steel         |
| DP06006R5      | 600mm  | 600mm | 17mm  | Free-Standing  | Mild Steel         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**