nVent CADDY Speed Link SLK with Loop, 2 mm Wire, 10 m Length

CATALOG NUMBER

SLK2L10LP

FEATURES

- Complete system includes wire, locking device and pre-assembled loop end fitting
- Easy and flexible solution attaches to building structures
- Wire rope wraps around structure and through loop for quick installation
- Ideal for attaching to purlins, beams and other structural members
- Works well in tight or confined spaces
- Loop attaches directly to pipe, ductwork or other hanging assemblies

PRODUCT ATTRIBUTES

Article Number: 196606
Material: Steel;Polypropylene;Zinc Alloy
Finish: Electrogalvanized
Static Load Safety Factor: 5:1
Wire Rope Diameter: 2 mm
Complies With: SMACNA HVAC-DCS
Wire Rope Length: 10m
Length (L): 101.6mm
Height (H): 55 mm
Width (W): 19 mm
Thickness (T): 12.5 mm
Angle (a): 90 ° Max
Static Load: 440N

DIAGRAMS







WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.