

# Hol-Sealers Hole Seal

Seal extra pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water with Hol-Sealers hole seals . Seals will cover any size or shape of hole from .19-in. diameter to maximum diameter shown in table. Can be used on enclosure walls up to .31-in. (8-mm) thick. Maintains enclosures Type rating 3R, 4, 4X (Stainless Steel version only) 12, and 13 when installed in an nVent HOFFMAN enclosure.



## INDUSTRY STANDARDS

UL 508A Component Recognized; Type 3R, 4, 12, 13; File No. E61997 (MS)

UL 508A Component Recognized; Type 3R, 4, 4X, 12, 13; File No. E61997 (SS)

Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 12, 13

NEMA/EEMAC Type 3R, 4, 12, 13

IEC 60529, IP66

Stainless Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 4X, 12, 13

NEMA/EEMAC Type 3R, 4, 4X, 12, 13

IEC 60529, IP66

## FEATURES

Available in multiple colors and sizes

Oil-resistant gasket provided

Steel model has plated stud (10-32x5/8) and wing nut

Stainless steel model has 300 series stainless steel stud (10-24x5/8) and wing nut

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material            | Finish        | Color | Color Code | Thickness |
|----------------|----------------|---------------------|---------------|-------|------------|-----------|
| AS056MSS       | 15506          | Stainless Steel 304 | Polished      |       |            | 1.5mm     |
| AS056M         | 15505          | Mild Steel          | Powder Coated | Gray  | ANSI 61    | 1.5mm     |
| AS056MFB       | 16485          | Mild Steel          | Powder Coated | Gray  | ANSI 61    | 1.5mm     |

| Catalog Number | Article Number | Material            | Finish        | Color      | Color Code | Thickness |
|----------------|----------------|---------------------|---------------|------------|------------|-----------|
| AS056MLG       | 16076          | Mild Steel          | Powder Coated | Light Gray | RAL 7035   | 1.5mm     |
| AS056CB        | 15645          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |
| ASPBGSS        | 59420          | Stainless Steel 304 | Polished      |            |            | 1.5mm     |
| ASPBG          | 59690          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |
| AS100LG        | 15576          | Mild Steel          | Powder Coated | Light Gray | RAL 7035   | 1.5mm     |
| AS100SS        | 59460          | Stainless Steel 304 | Polished      |            |            | 1.5mm     |
| AS100          | 59730          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |
| AS050          | 59700          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |
| AS050LG        | 15574          | Mild Steel          | Powder Coated | Light Gray | RAL 7035   | 1.5mm     |
| AS050SS        | 59430          | Stainless Steel 304 | Polished      |            |            | 1.5mm     |
| AS350SS        | 15961          | Stainless Steel 304 | Polished      |            |            | 1.5mm     |
| AS250SS        | 15957          | Stainless Steel 304 | Polished      |            |            | 1.5mm     |
| AS125LG        | 15578          | Mild Steel          | Powder Coated | Light Gray | RAL 7035   | 1.5mm     |
| AS150SS        | 59480          | Stainless Steel 304 | Polished      |            |            | 1.5mm     |
| AS400SS        | 15962          | Stainless Steel 304 | Polished      |            |            | 1.5mm     |
| AS125SS        | 59470          | Stainless Steel 304 | Polished      |            |            | 1.5mm     |
| AS075          | 59710          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |

Table 2/2

| Catalog Number | Article Number | Material            | Finish        | Color      | Color Code | Thickness |
|----------------|----------------|---------------------|---------------|------------|------------|-----------|
| AS150LG        | 15581          | Mild Steel          | Powder Coated | Light Gray | RAL 7035   | 1.5mm     |
| ASPB           | 59720          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |
| AS300SS        | 15958          | Stainless Steel 304 | Polished      |            |            | 1.5mm     |
| AS300          | 59780          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |
| AS150          | 59750          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |
| AS125          | 59740          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |
| AS400          | 59800          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |
| AS200          | 59760          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |
| ASPBSS         | 59450          | Stainless Steel 304 | Polished      |            |            | 1.5mm     |
| AS200SS        | 59490          | Stainless Steel 304 | Polished      |            |            | 1.5mm     |
| AS250          | 59770          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |
| AS075SS        | 59440          | Stainless Steel 304 | Polished      |            |            | 1.5mm     |
| ASPB LG        | 15582          | Mild Steel          | Powder Coated | Light Gray | RAL 7035   | 1.5mm     |
| AS350          | 59790          | Mild Steel          | Powder Coated | Gray       | ANSI 61    | 1.5mm     |
| AS200LG        | 15577          | Mild Steel          | Powder Coated | Light Gray | RAL 7035   | 1.5mm     |
| AS075LG        | 15575          | Mild Steel          | Powder Coated | Light Gray | RAL 7035   | 1.5mm     |

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**