

Side Plinths Mild Steel, PS



The extra space created by the plinth is closed off by using these panels in order to restrict access to this area.

FEATURES

Description: Side panels to cover the openings in the sides of the PF/PV plinths. Double folded panels for maximum strength. Compatible with combinable and semi-compact enclosure ranges.

Material: 1.5 mm steel plate.

Finish: RAL 7022 structured powder coating.

Pack quantity: 2 panels. Mounting accessories included with PF/PV.

Thickness: 1.5mm
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7022
Color: Umbra Gray

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Product Family	Enclosure Material
PS2100	PS2100	200mm	999mm	27mm	Free-Standing	Mild Steel
PS1060	PS1060	100mm	600mm	27mm	Free-Standing	Mild Steel
PS2080	PS2080	200mm	800mm	27mm	Free-Standing	Mild Steel
PS1040	PS1040	100mm	400mm	27mm	Free-Standing	Mild Steel
PS2050	PS2050	200mm	500mm	27mm	Free-Standing	Mild Steel
PS1080	PS1080	100mm	800mm	27mm	Free-Standing	Mild Steel
PS2030	PS2030	200mm	300mm	27mm	Free-Standing	Mild Steel
PS1100	PS1100	100mm	999mm	27mm	Free-Standing	Mild Steel
PS2040	PS2040	200mm	400mm	27mm	Free-Standing	Mild Steel
PS2060	PS2060	200mm	600mm	27mm	Free-Standing	Mild Steel
PS1050	PS1050	100mm	500mm	27mm	Free-Standing	Mild Steel
PS1030	PS1030	100mm	300mm	27mm	Free-Standing	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE