We connect and protect

3000 Beam Clamp Kit, 300 mm, 15 mm Max Flange



CATALOG NUMBER

3300EG

FEATURES

- Medium duty system
- Includes clamp and U channel

PRODUCT ATTRIBUTES

Article Number: 570410
Material: Steel
Finish: Electrogalvanized
Length (L): 300mm
Height (H): 15 mm
Width (W): 30 mm
Thickness (T): 2.5 mm
Flange Thickness (FT): 15 mm Max
Hole Size (HS): 13 mm
Static Load 1 (F1): 3700N
Static Load 2 (F2): 490N
Static Load 3 (F3): 390N
A: 40 mm
B: 100 mm
C: 150 mm
D: 25 mm

E: 31.5 mm

X: 10.5 x 25 mm

Screw Diameter (Sc): 8

Torque (TQ): 30 N·m

DIAGRAMS







WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.