

B18 Combination Box/Conduit Hanger



The nVent CADDY B18 Combination Box/Conduit Hanger presents an efficient and secure solution for the installation of electrical boxes and conduit in overhead applications by streamlining the process with a single-threaded rod drop. The system is designed to provide greater efficiency in the field with our class-leading range of nVent CADDY Conduit Clamps.

FEATURES

Scoreline breakaway feature can be easily modified by hand while maintaining UL listing

Eliminates need for offset bending conduit

Designed to be versatile and reusable

Labor and time savings due to built-in first means of support

NEC® & CEC compliant

Finish: Pregalvanized;nVent CADDY Armour
Material: Steel;Spring Steel




SPECIFICATIONS

Catalog Number	Outer Diameter (OD)	Hole Size (HS)	Hole Type	Screw Included	Screw Length (L)	Length (L)	Width (W)
16MB18A		6.4 mm	Plain	No		457.2mm	53.34 mm
6MB18A		6.4 mm	Plain	No		457.2mm	53.34 mm
812MB18A	18 - 30 mm	6.4 mm	Plain	No		457.2mm	53.34 mm
812MB18S				Yes	14.3mm	457.2mm	53.34 mm

ADDITIONAL PRODUCT DETAILS

NEC® 300.11 requires dedicated drop wire/rod. For single and multiple runs of conduit.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

