

Conduit Trapeze CCT125

The nVent CADDY Conduit Trapeze CCT125 range is a fast and cost-effective method to install larger branch circuits of conduit in overhead trapeze installations. The CCT125 series reduces installation time and material cost by eliminating the need for traditional fasteners, making it an ideal solution for contractors looking to maximize installation efficiency.

FEATURES

Ideal for larger branch circuits

Accommodates 3/8" and 1/4" threaded rod trapeze drops

Up to 25% material savings over traditional methods

Reduces installation time up to 50%

Complies with UL® 2239

Finish: Pregalvanized
Material: Steel



SPECIFICATIONS

Table 1/2

Catalog Number	Number of Conduits	Rod Size (RS)	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Hole Size 3 (HS3)	Hole Size 4 (HS4)
CCT125X96	48	10	11.11 mm	7.14 mm	3.17mm	41.27mm
CCT125X36	18	10	11.11 mm	7.14 mm	3.17mm	41.27mm
CCT125X24	12	10	11.11 mm	7.14 mm	3.17mm	41.27mm
CCT125X12	6	10	11.11 mm	7.14 mm	3.17mm	41.27mm

Table 2/2

Catalog Number	Length 1 (L1)	Length 2 (L2)	Length 3 (L3)	Length 4 (L4)	Length (L)
CCT125X96	2489 mm	2438 mm	50.8mm	50.8 mm	2489mm
CCT125X36	914 mm	965 mm	50.8mm	50.8 mm	965mm
CCT125X24	610 mm	660 mm	50.8mm	50.8 mm	660mm
CCT125X12	304.8 mm	355.6 mm	50.8mm	50.8 mm	356mm

ADDITIONAL PRODUCT DETAILS

For 3/8" and 1/4" threaded rod trapeze drops, use washer or SN25 for 1/4" threaded rod applications.

The table contains maximum conduit size values.

DIAGRAMS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America	Europe	Europe	APAC
+1.800.753.9221	Netherlands:	Germany:	Shanghai:
Option 1 – Customer Care	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
Option 2 – Technical	France:	Other Countries:	Sydney:
Support	+33 800 901 793	+31 13 5835404	+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

