

nVent CADDY Pyramid Crossover Ladder, 50°

FEATURES

Standard angle ladders provide easy changes in elevation

Interchangeable components are easily assembled yielding labor-saving and quick installations

nVent CADDY Pyramid bases provide superior load distribution and roof membrane compatibility

Foam bottom offers low abrasion interface for better roof membrane protection

Aluminum construction designed to withstand harsh environments

Walking surfaces with serrated tread provides maximum slip resistance and drainage

Compliant with OSHA, Cal/OSHA and ANSI® standards

Material: Aluminum;Polypropylene;Polyethylene

SPECIFICATIONS

Catalog Number	Walkway Height	Number of Steps	Height (H)	Width (W)	Depth (D)	A	Static Load
PCL50S2	508 mm	2	1574 mm	1331 mm	581mm	241 mm	2200N
PCL50S3	762 mm	3	1828 mm	1331 mm	918mm	241 mm	2200N
PCL50S4	1016 mm	4	2082 mm	1331 mm	1131mm	241 mm	2200N
PCL50S5	1270 mm	5	2336 mm	1331 mm	1344mm	241 mm	2200N
PCL50S6	1524 mm	6	2590 mm	1331 mm	1558mm	241 mm	2200N

ADDITIONAL PRODUCT DETAILS

Clearance of walkway is 3" less than the walkway height.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

