

nVent CADDY Rod Lock Prefabricated Strut Assembly



nVent CADDY Rod Lock Prefab Strut Assemblies increase overall productivity and job site safety when working with trapeze and threaded rods. With our innovative nVent CADDY "push-to-install" technology, quickly create, install and adjust multi-level trapeze assemblies by simply pushing threaded rod through the mounting hole and setting into place without the need for tools.

Ready to use out-of-the-box, the Rod Lock Prefab Assemblies quickly install on-site or can be prefabricated in advance. To further expedite the process and meet contractors' specific needs, nVent CADDY offers Made-to-Order (MTO) options that are fully customizable. Contact your local nVent CADDY Representative for more information about our prefabricated options.

FEATURES

Slot-to-slot configuration allows cartridges to adjust up to ¼ in on each end from the center of the slot

Accommodates slight variation in rod-to-rod position of the trapeze

Lock nut can easily be tightened without the use of tools

Works with all accessories that fit standard A type strut channels


Strut Type: A (41 x 41 mm)
Finish: Electrogalvanized; Pregalvanized
Material: Steel

SPECIFICATIONS

Catalog Number	Length (L)	Thickness (T)	A	B	X	Ultimate Static Load (F)
CRLP13SSA12L20	508mm	2.6 mm	457.2 mm	0.0 - 22.225 mm	15 x 28 mm	8451mm
CRLP13SSA12L30	762mm	2.6 mm	711.19 mm	0.0 - 22.225 mm	17 x 28 mm	5338mm
CRLP13SSA12L24	609.6mm	2.6 mm	558.8 mm	0.0 - 22.225 mm	16 x 28 mm	6895mm
CRLP15SSA12L24	609.6mm	2.6 mm	558.8 mm	0.0 - 22.225 mm	16 x 28 mm	6895mm
CRLP15SSA12L20	508mm	2.6 mm	457.2 mm	0.0 - 22.225 mm	15 x 28 mm	8451mm

Catalog Number	Length (L)	Thickness (T)	A	B	X	Ultimate Static Load (F)
CRLP15SSA12L30	762mm	2.6 mm	711.19 mm	0.0 - 22.225 mm	17 x 28 mm	5338mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

