

Portable Rail Grinder, Two-Cycle Gas-Powered



FEATURES

Strong 39cc two-cycle engine

Power head handle incorporates base plate to protect engine from damage

Lightweight design

Anti-vibration handle reduces operator fatigue and helps provide proper balance while operating the grinder

Stronger shaft increases durability of operation

Increased grinding wheel stability reduces vibration and wear during operation

One piece of equipment to grind head and web

Maximum wheel speed is 6,000 rpm

Adjustable grinding wheel guard rotates 360° and allows operation in tight areas

SPECIFICATIONS

Catalog Number	Type	Unit Weight
SBG150	Grinder Only	8.2 kg
SBG150WC	Grinder with Storage Case	14.6 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE