

Side Panels Stainless Steel, SPMS

These side panels will ensure that the ingress protection is maintained, which means that the electrical components will operate without any disturbances and protect personnel from injuries.

FEATURES

Description: Easy one man assembly. Sealed by an extruded, one piece polyurethane gasket and mounted with 8 screws and new patented retainers.

Protection: IP 55, TYPE 12, 13 in combination with MCSS. IP66, TYPE 4X, 12 in combination with MCSS-HP.

Pack quantity: 2 panels with mounting accessories.

Material: 1.5 mm AISI 304 / AISI 316L pre-grained stainless steel.

Finish: 400 pre-grained stainless steel.

Thickness: 1.5mm
Finish: Brushed

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Product Family	Enclosure Material
SPMS2006-316		1964mm	18mm	562mm	Free-Standing	Stainless Steel
SPMS1805	SPMS1805	1764mm	18mm	462mm	Free-Standing	Stainless Steel
SPMS2006 	SPMS2006	1964mm	18mm	562mm	Free-Standing	Stainless Steel
SPMS1805-316		1764mm	18mm	462mm	Free-Standing	Stainless Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.