

PCR Perforated C-Shaped Profile



FEATURES

Rapid assembly of all kinds of frameworks

High mechanical resistance

High corrosion resistance

Conforms to EN 60715 and DIN 46277

RoHS compliant

Finish: Electrogalvanized

Material: Steel



SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Height (H)	Width (W)	Length (L)	Thickness (T)	A
PCR40X20-2M	557500	40 mm	20 mm	2000mm	1.5 mm	24 mm
PCR30X15-3M	557780	30 mm	15 mm	3000mm	1.5 mm	15 mm
PCR35X35-3M	557790	35 mm	35 mm	3000mm	2 mm	16 mm
PCR35X35-2M	557520	35 mm	35 mm	2000mm	2 mm	16 mm

Table 2/2

Catalog Number	Article Number	B	C	D	Unit Weight
PCR40X20-2M	557500	7 mm	18 mm	8.2 mm	2.5 kg
PCR30X15-3M	557780	7 mm	18 mm	8.2 mm	2.4 kg
PCR35X35-3M	557790	7 mm	18 mm	8.2 mm	4.5 kg
PCR35X35-2M	557520	7 mm	18 mm	8.2 mm	3 kg



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE