


EuropacPRO Cover Plate for Bolting to Rugged Side Panel



A cover plate is used for electromagnetic shielding or as mechanical protection.

FEATURES

Perforation degree 58%

Rack Width: 84HP
Material: Aluminum
Product Type: Cover Plate
Product Family: EuropacPRO
Finish: Passivated
Type: Perforated
Works With: Subracks



SPECIFICATIONS

Catalog Number	Depth	Package Quantity	Package Unit	Torque
24568-004	175mm	2	Pair	2.1N·m
24568-036	277.75mm	2	Pair	2.1N·m
24568-032	275mm	2	Pair	2.1N·m
24568-020	355mm	2	Pair	2.1N·m
24568-016	295mm	2	Pair	2.1N·m
24568-012	295mm	2	Pair	2.1N·m
24568-008	235mm	2	Pair	2.1N·m

ADDITIONAL PRODUCT DETAILS

A top cover locking mechanism is optionally available that also fixes the top cover in the front and rear guide rail.

4 stainless steel EMC contact strips per subrack are required for shielding, please order separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE