ER Stainless Steel Mast



FEATURES

Designed to mount nVent ERICO System 1000 and nVent ERICO System 3000 air terminals

Material: Stainless Steel 304 (EN 1.4301)

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Product	Thread Size (TS)	Length (L)	Thickness (T)	Outer Diameter (OD)
ER22000SS	702265	Mid Mast Section	1 1/16" UN	2254.25mm	3.05 mm	31.75 mm
ER33000SS	702280	Lower Mast Section		2997.2mm	3.05 mm	38.1 mm
ER23000SS	702270	Mid Mast Section	1 1/16" UN	3244.85mm	3.05 mm	31.75 mm
ER32000SS	702275	Lower Mast Section		2006.6mm	3.05 mm	38.1 mm
ER11000SS	702255	Upper Mast Section	3/4" UNC	1253.2mm	4.78 mm	25.4 mm

Table 2/2

Catalog Number	Article Number	Hardware Included	Unit Weight
ER22000SS	702265	Yes	4.9 kg
ER33000SS	702280	Yes	7.3 kg

Catalog Number	Article Number	Hardware Included	Unit Weight
ER23000SS	702270	Yes	7.3 kg
ER32000SS	702275	Yes	5.3 kg
ER11000SS	702255	No	3.5 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Our powerful portfolio of brands:
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.