We connect and protect

Wire Basket Tray C Bracket, 300 mm, Black, Electrogalvanized

CATALOG NUMBER

WBTCBRKT12BA

Engineered for efficiency and adaptability, the nVent CADDY Wire Basket Tray C Bracket is a fast and simple component of modern cable management systems. Designed to streamline installation processes, this bracket excels in both hard-ceiling and two-tier wall mounting scenarios, offering contractors a reliable and time-saving solution for complex environments

The C Bracket ensures that high-performance, low-voltage and data cables are securely supported with minimal effort. Simply pair with the nVent CADDY Wire Basket Tray Washer Support or nVent CADDY Wire Basket Tray Ground Splice and quickly fasten it to the wire basket tray to create a robust framework for layered tray runs. This combination not only enhances structural integrity but also provides the flexibility needed for multi-tiered installations, accommodating evolving infrastructure demands without compromising safety or performance.

FEATURES

- Easy-to-use quick connect feature
- Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice
- Side load access for cable installation
- Ideal for ceiling, wall and channel installations
- Side load access for simple cable installation

CE

PRODUCT ATTRIBUTES

- Material: Steel
- Finish: Electrogalvanized
- Color: Black

Height (H): 200.03 mm

Width (W): 41.4 mm

Length (L): 350.52mm

Length 1 (L1): 139.7 mm

Hole Size (HS): 7.137 mm

Unit Weight: 1.025 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.